



Pass and Seymour
4-in Round Ceiling Box
Part No. S120RFAN



Ceiling Fan Box with two captive mounting nails. Standard Grade.
Four Auto/Clamps. 30 pack.

Features & Benefits

Constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive.

UL Listed for fan and fixture support.

Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.

Dual mounting accepts fans or fixtures with 2.75 inch or 3.5 inch straps.

Phillips-head screws (#10-32 x 3 inch) mount the fan or fixture directly to the metal bracket.

For covering patents, see www.legrand.us/patents.

Auto Clamp cable clamps molded in, hold wire securely in box.

Large, 20.25 cubic inch capacity for extra wiring space.

Angled, rugged, metal mounting bracket safely and securely fastens fans or fixtures to the building structure.

Fan mounts directly to bracket through box with #10-32 screws (provided).

Ringed nails for tighter grip.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007158144	Country Of Origin	United States
Features	Auto Clamps, Fan Rated, Fixture Rated, Threaded Mounting Holes	Installation Location	Ceiling
Number of Knockouts	4	Application Sector	Commercial, Residential
Standard	Residential/Commercial	Warranty Type	1-Year Limited Warranty

Type	Ceiling Box		
Dimensions			
Cubic Capacity	20.25 in³		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Indoor/Outdoor	Indoor	Cable Entry	Back, Side
Box Shape	Round	Mounting Type	Stud Mount