



Wiremold  
Plugmold 3 ft. Self Test GFCI 5-Outlet Power Strip, Stainless Steel  
Part No. S20GB306TRGFI6



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

## Features & Benefits

Built-in GFCI protection. Provides GFCI protection for all outlets on the Plugmold strip and all devices plugged into them. Great for residential kitchens with multiple small appliances, as well as laboratories.

Multiple colors and finishes. Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

Tamper-resistant receptacles. Patented shutter system prevents improper insertion of foreign objects. Meets 2017 National Electrical Code® Tamper-Resistant requirements.

## Specifications

### General Info

Product Line	Wiremold	Color	Silver
UPC Number	786776188066	Country Of Origin	United States
Number of Receptacles	5	Application Sector	Residential/Commercial
Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7	Type	Plugmold

### Dimensions

Product Width US	36.0 in	Product Weight US	1.79 lb
Product Volume US	44.01 cu in	Product Depth US	0.75 in
Product Height US	1.63 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

Technical Information

Frequency Rating	60 Hz	Amperage	15 A
------------------	-------	----------	------

Enclosure Type	Stainless Steel	Voltage	125.0 V
----------------	-----------------	---------	---------