



Pass and Seymour  
Screw Mount Steel Stud Box with Quick/Click  
Part No. S354RACS



Triple Gang, Screw Mount Steel Stud Box with captive Combo Head Self-Tapping Mount Screws on Each End. Six Auto/Clamps on Each End. 50 pack.

## Features & Benefits

Available in single, single deep, two, three and four gang, and 4 inch round ceiling boxes.

Single gang include Quick/Entry feature.

Screws have combination Hex/Phillips washer heads.

Can be used for steel, aluminum, or wood studs.

Locator ribs ensure proper alignment on stud and proper offset depth.

All multi-gang and ceiling boxes include exclusive Auto/Clamp feature.

Specially designed drill point rapidly penetrates medium gauge steel studs.

Quick/Click feature on wall boxes offers fast and dependable installation of devices.

Molded of high-impact thermoplastic.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007652741	Country Of Origin	United States
Features	Auto Clamps, Quick Entry	Installation Location	Wall
Number of Knockouts	12	Application Sector	Commercial, Residential
Standard	Residential/Commercial	Warranty Type	1-Year Limited Warranty
Type	Outlet Box		

Dimensions

Product Width US	5.781 in	Product Depth US	3.0 in
Product Length US	3.969 in	Cubic Capacity	54 in <sup>3</sup>

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Gangs	3	Indoor/Outdoor	Indoor
Cable Entry	Back, Bottom, Top	Box Shape	Rectangular
Mounting Type	Screw Mount		