



Pass and Seymour  
Clock Hanger Receptacles, Recessed with Stainless Steel Wall Plate, 15A, 125V  
Part No. S3733SS



Clock Hanger Receptacles, Recessed with Stainless Steel Wall Plate, 15A, 125A

## Features & Benefits

Single recessed receptacle.

Stainless steel: wall plate.

## Specifications

### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Commercial	Standard	UL 498

### Dimensions

Product Width US	2.74 in	Product Depth US	1.88 in
Product Height US	4.478 in		

### Technical Information

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Voltage	115.0 V		