



Pass and Seymour
2-Gang Chrome Wall Plate, 1 Power Outlet Receptacle Opening
Part No. S3863C



TwoGang Power Outlet Receptacle Opening, 2.4688 hole for 2.375 diameter device -4 mtg. holes, Smooth Metal.

Features & Benefits

Chrome: .040" thick.

Lacquered to prevent corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

Specifications

General Info

| | | | |
|-------------------|-------------------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Chrome |
| Finish | Metallic | UPC Number | 785007138276 |
| Country Of Origin | United States | Wall Plate Size | Standard Size |
| Wall Plate Type | Outlet, Round | Application Sector | Commercial, Residential |
| Warranty Type | 1-Year Limited Warranty | Type | Wall Plate |

Dimensions

| | | | |
|---------------------------------------|----------|------------------|---------------|
| Product Width US | 4.56 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus Listed | Yes | | |
| Additional Information | | | |
| Product Environmental Profile | Yes | | |
| Technical Information | | | |
| Thickness | 0.04 in | Number of Gangs | 2 |
| Indoor/Outdoor | Indoor | Mounting Type | Strap Mounted |
| Orientation | Vertical | | |