



Pass and Seymour  
2-Gang Aluminum Wall Plate, 1 Toggle Switch Opening, 1 Decorator Opening  
Part No. SA126



Smooth Metal Wall Plate Aluminum

## Features & Benefits

Aluminum: .040" thick.

Lustrous satin finish.

Lacquered to prevent corrosion.

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Aluminum
Finish	Satin	UPC Number	785007137996
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Combination, Decorator, Toggle Switch	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Thickness	0.04 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		