



Pass and Seymour  
2-Gang Aluminum Wall Plate, 2 Toggle Switch Openings  
Part No. SA2



Smooth Metal Wall Plate 2-Gang Toggle Aluminum

## Features & Benefits

Aluminum: .040" thick.

Lacquered to prevent corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Lustrous satin finish.

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Aluminum
Finish	Satin	UPC Number	785007138108
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Toggle Switch	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
------------------	---------	------------------	--------

Product Height US	4.5 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.04 in	Number of Gangs	2
-----------	---------	-----------------	---

Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
----------------	--------	---------------	-------------

Orientation	Vertical
-------------	----------