



Pass and Seymour  
2-Gang Polished Brass Wall Plate, 2 Duplex Receptacle Openings  
Part No. SB82PBCC5



Smooth Metal Wall Plate 2gang Duplex Polished Brass

## Features & Benefits

Polished Brass: .040" thick.	70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.
Lacquered to prevent corrosion.	Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.	Packaged in protective film, with finish-matching screws.
Variety of special plated finishes.	Paintable to match plastic plates.
Can be silk-screened or engraved, and custom punched with over 300 opening styles.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brass
Finish	Metallic	UPC Number	785007050592
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Duplex Receptacle	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Thickness	0.04 in	Indoor/Outdoor	Indoor
-----------	---------	----------------	--------

---

Mounting Type	Box Mounted	Orientation	Vertical
---------------	-------------	-------------	----------

---