



This MSA Compliant SFP transceiver provides 1000Base-TX throughput up to 100m over a copper connection using a RJ-45 connector. It is built to MSA standards and is uniquely serialized and data-traffic and application tested to ensure that they will integrate into your network seamlessly. Our TX transceiver modules support 10/100/1000Mbps auto-negotiation and can be configured to fit your needs. It is built to meet or exceed the specifications of MSA Compliant, as well as to comply with MSA (Multi-Source Agreement) standards to ensure seamless network integration. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits

Supports data rates up to 1000Mbps	SFP (mini-GBIC) transceiver module
Transceiver type TX allows for connections up to 100m	RJ45 port designed for use with a copper patch cable

Specifications

General Info

Product Line	Legrand	Color	Silver
UPC Number	757120668114	Country Of Origin	United States
Application Sector	Commercial/Industrial	Type	Transceiver

Additional Information

RoHS Conformant	Yes	Product Has Potential to Contribute to LEED	Yes
-----------------	-----	---	-----