



Ortronics

Cisco SFP-10G-SR-S Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)

Part No. SFP-10G-SR-S-L



Cisco SFP-10G-SR-S Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)

Features & Benefits

Guaranteed Compatible

In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate

Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty

For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate

Extensive inventory guarantees same day shipping.

Full Service Technical Support

Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line	Ortronics	Country Of Origin	China
Type	Transceiver		

Technical Information

Cable Type	Multimode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Data Transfer Rate	10 Gbps
Connector Type	LC Duplex	Wavelength	850nm
Form Factor	SFP+		