



Meraki SFP-10GB-SR Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)



Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty: For more information by product line, visit our [Warranty page](#).

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875068730
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

Dimensions

Product Width US	13.7 mm	Product Depth US	58.4 mm
Product Height US	8.5 mm		

Technical Information

Fiber Optic Cable Type	Multimode	Max Distance Support	300 m
Operating Temperature Min	-40 °C	Operating Temperature Max	85 °C
Data Transfer Rate	10 Gbps	Connector Type	LC Duplex
Form Factor	SFP+		