




Pass and Seymour
1-Gang 302/304 Stainless Steel Wall Plate, Pad Printed "Gas Burner, On/Off" with Toggle Opening, Painted Red
Part No. SS1GBRED

Single-Gang toggle. Smooth 302/304 Stainless Steel Painted with Fill.



Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.

Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Finish	Metallic	UPC Number	785007136876
Country Of Origin	United States	Features	Pad Printed
Wall Plate Size	Standard Size	Wall Plate Type	Toggle Switch
Application Sector	Commercial, Residential	Standard	CSA
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

Dimensions

Product Width US	2.75 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Thickness	0.032 in	Number of Gangs	1
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		