



Smooth Metal Wall Plate 5gang Decorator 302/304 Stainless Steel

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032"^{nominal thickness}.
Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.
Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

| | | | |
|--------------|----------------|--------------------|------------------------|
| UPC Number | 785007136005 | Country Of Origin | United States |
| Product Line | Pass & Seymour | Application Sector | Residential/Commercial |
| Standard | UL 514 | | |

Listing Agencies / 3rd Party Agencies

CSA Listed Yes

Technical Information

Number of Gangs 5 Cutout Decorator

Thickness

0.032 in
