



Legrand

Combination Openings, 4 Toggle Switch & 1 Duplex Receptacle, Five Gang,
302/304 Stainless Steel Painted Ivory
Part No. SS481



Smooth Metal Wall Plate 4gang Toggle 1gang Duplex 302/304 Stainless Steel Painted Ivory

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic; .032" nominal thickness.

Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

UPC Number 785007136999

Countries Of Origin United States

Product Line Pass & Seymour

Application Sector Residential/Commercial

Standard UL 514

Listing Agencies / 3rd Party Agencies

CSA Listed Yes

Technical Information

Cutout Toggle and Receptacle

Thickness 0.032 in

Gangs 5