

Smooth Metal Wall Plate, 8-Gang Blank, Box Mounted,
302/304 Stainless Steel



Features & Benefits

| | |
|---|--|
| Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness. | Brushed finish. |
| This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. | Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist. |
| Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide. | Packaged in protective film, with finish-matching screws. |
| Variety of special plated finishes. | Paintable to match plastic plates. |
| Can be silk-screened or engraved, and custom punched with over 300 opening styles. | |

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|---------------|
| Product Line | Pass & Seymour | Country Of Origin | United States |
| Application Sector | Residential/Commercial | Standard | CSA |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 15.44 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

Technical Information

| | | | |
|-----------------|-------|-----------|----------|
| Cutout | Blank | Thickness | 0.032 in |
| Number of Gangs | 8 | | |
