



Double gang wall plate with one center outlet. Box mounted. Smooth 302/304 Stainless Steel.

Features & Benefits

| | |
|---|--|
| Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness. | Brushed finish. |
| This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. | Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist. |
| Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide. | Packaged in protective film, with finish-matching screws. |
| Variety of special plated finishes. | Paintable to match plastic plates. |
| Can be silk-screened or engraved, and custom punched with over 300 opening styles. | |

Specifications

| General Info | | | |
|---------------------------------------|---------------------------|-------------------|---------------|
| Product Line | Pass & Seymour | Country Of Origin | United States |
| Application Sector | Residential/Commercial | Standard | CSA |
| Dimensions | | | |
| Product Width US | 4.56 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus Listed | Yes | | |
| Technical Information | | | |
| Cutout | Telephone or Cable Outlet | Thickness | 0.032 in |
| Number of Gangs | 2 | | |