



## Pass and Seymour

Two Gang with Center Opening Wall Plate, Single Receptacle Opening, 302/304 Stainless Steel  
Part No. SS747



Double gang, Single receptacle centered opening. 302/304 Stainless steel.

### Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.

Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

### Specifications

#### General Info

UPC Number	785007136289	Country Of Origin	United States
------------	--------------	-------------------	---------------

Product Line	Pass & Seymour	Application Sector	Residential/Commercial
--------------	----------------	--------------------	------------------------

Standard	UL 514
----------	--------

#### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

#### Technical Information

Cutout	Single Receptacle	Thickness	0.032 in
--------	-------------------	-----------	----------