



Pass and Seymour Communication Plate, Horizontal-Split for Television and Cable Lead-In, Two Gang with Center Opening, 302/304 Stainless Steel Part No. SS787

Double gang, Single centered outlet, horizontal split wall plate for television or cable lead in. Also furnished for strap mounting. Catalog #S788 with two #340 yokes. Box mounted removable 5/8" ID grommet in 7/8" hole. Smooth 302/304 Stainless Steel.



Features & Benefits

Type 302/304 Stainless Steel, non-magnetic. .032" nominal thickness.

Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Packaged in protective film, with finish-matching screws.

Variety of special plated finishes.

Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

UPC Number 785007136340 Country Of Origin United States

Product Line Pass & Seymour Application Sector Residential/Commercial

Standard UL 514

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Cutout Television or Cable Lead-In Thickness 0.032 in