



## Features & Benefits

Tough, impact-resistant thermoplastic housing.

No de-rating required in multi-gang operations (700W).

Uses conventional 3-way wiring when used in conjunction with a 3-way switch.

Returns lights to previous level after a power failure.

Lifetime warranty.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	TSD1103P
Color	Brown	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	RoHS

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Wattage	1100 W	Voltage	120.0 V
Load	Incandescent	Environmental Conditions	Humidity: Less than 95% non condensing

