



Features & Benefits

Tough, impact-resistant thermoplastic housing.

No de-rating required in multi-gang operations (700W).

Uses conventional 3-way wiring when used in conjunction with a 3-way switch.

Returns lights to previous level after a power failure.

Lifetime warranty.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TSD1103PBK
Color	Black	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	RoHS
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Wattage	1100 W	Voltage	120.0 V

Load	Incandescent	Environmental Conditions	Humidity: Less than 95% non condensing
------	--------------	--------------------------	---
