



Features & Benefits

- Tough, impact-resistant thermoplastic housing.

Uses conventional 3-way wiring when used in conjunction with a 3-way switch.

Lifetime warranty.
- No de-rating required in multi-gang operations (700W).

Returns lights to previous level after a power failure.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TSD1103PLA
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	RoHS	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Wattage	1100 W	Voltage	120 V
Load	Incandescent	Environmental Conditions	Humidity: Less than 95% non condensing