



Pass and Seymour

Discontinued - Trademaster CFL/LED/Incandescent Single Pole/3-Way Toggle Dimmer, Ivory | Sub TSDCL303PI
Part No. TDCL453PI



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control. The TDCL453P is convenient to operate with a standard ON/OFF toggle switch and separate dimming wheel for precise dimming control. Use specific suffix for color: W- white, BK- black, LA- light almond, I- ivory and no suffix for brown.

Features & Benefits

- Tough, impact-resistant thermoplastic housing.
- Power-failure memory.
- Superior heat management: no time wasting break off tabs.
- Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.
- Preset, Single Pole/3-Way
- For covering patents, see www.legrand.us/patents.
- Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------------|------------------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | TSDCL303PI |
| Color | Ivory | Country Of Origin | China |
| Application Sector | Residential | Standard | RoHS, CSA Listed, UL Listed, cULus |
| Type | Dimmer | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------|--------------|------------|------------------------|
| Frequency Rating | 120VAC 60 Hz | Connection | Screw Terminals |
| Amperage | 1.6 A | Wattage | 450 W |
| Voltage | 120 V | Load | LED, CFL, Incandescent |

| | |
|--------------------------|---|
| Environmental Conditions | Humidity: Less than 95% non condensing |
|--------------------------|---|
