



Pass and Seymour
Discontinued - Trademaster Toggle De-Hummer Fan Speed Control, Brown | Sub TSDDH163P
Part No. TDDH163P



Features & Benefits

Tough, impact-resistant thermoplastic housing.	Power-failure memory.
Superior heat management: no time wasting break off tabs.	Exclusive, screw-pressure-plate back wire terminals eliminates wire nuts.
Preset, Single Pole/3-Way	For covering patents, see www.legrand.us/patents .
Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz.	

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TSDDH163P
Color	Brown	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	cULus, RoHS

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
Amperage	1.6 A	Voltage	120.0 V

Environmental Conditions	Humidity: Less than 95% non condensing
--------------------------	---
