




Ortronics
Clarity 10G TracJack, T568A/B, 180 degree, Black
Part No. TJ610-00



Clarity 10G TracJack, ETL tested as part of 100-meter 10 Gig channel solution. Front-loading and front removable. Universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned with synchronized reactance to Clarity 10G patch cords for optimum performance with minimized internal and alien crosstalk.

Features & Benefits

Recessed design: Provides a more flush aesthetic look.	Meets Category 6A component standard: Ensures standards compliance.
Center tuned synchronized reactance design: Transparent interface with Clarity 10G cords.	Easy lace IDC housing: Reduces wiring time.
Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.	Front removable: Less intrusive access for adds, moves, changes
Standard TracJack footprint: Fits in all TracJack faceplates and housings.	Icon compatible, 10G Marking on jack face: Supports 606 designation requirements.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875590675
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL Standard	Type	Jack

Dimensions

Product Width US	0.73 in	Product Depth US	1.1 in
Product Height US	0.92 in		

Additional Information

RoHS Conformant

Yes

Product Environmental Profile

Yes
