



Clarity 10G TracJack, ETL tested as part of 100-meter 10 Gig channel solution. Front-loading and front removable. Universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned with synchronized reactance to Clarity 10G patch cords for optimum performance with minimized internal and alien crosstalk.

Features & Benefits

Recessed design: Provides a more flush aesthetic look.

Meets Category 6A component standard: Ensures standards compliance.

Center tuned synchronized reactance design: Transparent interface with Clarity 10G cords.

Easy lace IDC housing: Reduces wiring time.

Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.

Front removable: Less intrusive access for adds, moves, changes

Standard TracJack footprint: Fits in all TracJack faceplates and housings.

Icon compatible, 10G Marking on jack face: Supports 606 designation requirements.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875611837
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL Standard	Type	Jack

Additional Information

RoHS Conformant	Yes
-----------------	-----