



Ortronics
Clarity 10G TracJack, T568A/B, 180 degree, Green
Part No. TJ610-45



Clarity 10G TracJack, ETL tested as part of 100-meter 10 Gig channel solution. Front-loading and front removable. Universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned with synchronized reactance to Clarity 10G patch cords for optimum performance with minimized internal and alien crosstalk.

Features & Benefits

Recessed design: Provides a more flush aesthetic look.	Meets Category 6A component standard: Ensures standards compliance.
Center tuned synchronized reactance design: Transparent interface with Clarity 10G cords.	Easy lace IDC housing: Reduces wiring time.
Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.	Front removable: Less intrusive access for adds, moves, changes
Standard TracJack footprint: Fits in all TracJack faceplates and housings.	Icon compatible, 10G Marking on jack face: Supports 606 designation requirements.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875620792
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	UL Standard	Type	Jack

Dimensions

Product Width US	0.73 in	Product Depth US	1.1 in
Product Height US	0.92 in		

Additional Information

RoHS Conformant

Yes
