



High-profile Brass Cover, fits any floor finish - including carpeting, linoleum, tile floors includes 885 15A, 125A Decorator Duplex receptacle and will accept any decorator device. Cover includes captive screws to prevent loss. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.

Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.

Meets UL514(c) scrub water exclusion test.

Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.

UL and cUL Listed. Captive screws on TM1542 Series -- screws will not be lost -- new.

Durable construction, impact, and scratch resistant PVC construction.

Auto/Clamps and knockouts on both sides of box.

Threaded device mounting holes.

Ready for low-voltage wiring, drill guides on underside of cover.

Made in USA.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brass
UPC Number	785007013085	Country Of Origin	United States
Cover Type	Tamper-Resistant	Features	Durable, Hinged Cover
Application Sector	Commercial, Residential	Standard	UL listed
Type	Floor Box cover		

### Listing Agencies / 3rd Party Agencies

cULus Listed      Yes

### Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Mounting Type	Box Mounted	Box Cover Position	Horizontal, Vertical
Number of Outlets	1		