



Low-Profile Brass Cover requires minimum 3/8-inch hardwood floor thickness. Includes 885 15A, 125A Decorator Duplex receptacle and will accept any decorator device.

Features & Benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Meets UL514(c) scrub water exclusion test.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- UL and cUL Listed.
- Made in USA.
- Durable construction, impact, and scratch resistant PVC construction.
- Auto/Clamps and knockouts on both sides of box.
- Threaded device mounting holes.
- Ready for low-voltage wiring, drill guides on underside of cover.
- Captive screws on TM1542 Series -- screws will not be lost -- new.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
Country Of Origin	United States	Application Sector	Residential/Commercial
Standard	UL listed		

Dimensions

Cubic Capacity	38 cu in
----------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Number of Outlets	1
---------------------	-----	-------------------	---
