



Thermoplastic Cover Includes 15 amp 125 volt Decorator receptacle, matching detachable and replaceable hinged door threaded device-mounting holes drill guides for low-voltage poke-through holes accepts any Decorator device mounts on carpeting, hardwood, linoleum, tile floors Four mounting/leveling screws. Gray. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Durable construction, impact, and scratch resistant PVC construction.
- Auto/Clamps and knockouts on both sides of box.
- Threaded device mounting holes.
- Ready for low-voltage wiring, drill guides on underside of cover.
- Made in USA.
- Hinged door is removable and easily replaceable.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Meets UL514(c) scrub water exclusion test.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- UL and cUL Listed. Captive screws on TM1542 Series -- screws will not be lost -- new.

Specifications

General Info

UPC Number	785007108811	Country Of Origin	United States
Product Line	Pass & Seymour	Application Sector	Residential/Commercial
Standard	UL listed		

Dimensions

Cubic Capacity	38 cu in
----------------	----------

Technical Information

Number of Outlets	1
-------------------	---