



Pass and Seymour  
Spec Grade Decorator Maintained Contact Switch, Light Almond  
Part No. TM811DTMALA



Specification Grade, Double-Throw, Maintained Contact Switch, 15A, 120 volts.

## Features & Benefits

Impact-resistant face and body.	Fully rounded back body protects wires from being damaged by sharp edges.
Clear identification of circuits.	External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
Ground screw position under the end of the strap minimizes the risk of contact.	Full wraparound metal strap with lock-in tabs.
Patented split circuit tab -- easily accessible, and can be reinstalled without a tool.	Unique "Up/Down" switches match the look and feel of standard Decorator switches.
Largest breadth of 15 amp offering.	All screws are tri-drive.
Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007157611
Country Of Origin	China	Features	Decorator Style
Application Sector	Commercial, Residential	Standard	UL 20
Type	Combination		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage	15 A	Wire Size	#14 - #10 AWG
----------	------	-----------	---------------