

Specification Grade, Double-Throw, Maintained Contact Switch, 15A, 120 volts.



Features & Benefits

Impact-resistant face and body.	Fully rounded back body protects wires from being damaged by sharp edges.
Clear identification of circuits.	External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
Ground screw position under the end of the strap minimizes the risk of contact.	Full wraparound metal strap with lock-in tabs.
Patented split circuit tab -- easily accessible, and can be reinstalled without a tool.	Unique "Up/Down" switches match the look and feel of standard Decorator switches.
Largest breadth of 15 amp offering.	All screws are tri-drive.
Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.	For covering patents, see www.legrand.us/patents .

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	UL 20
Type	Combination		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage

15 A
