



radiant Collection  
radiant® 15A Tamper-Resistant USB Outlet, Black  
Part No. TM826USBBKCC6



Get a full battery for your phones, tablets and more with the convenience of built-in charging. This tamper-resistant USB outlet includes two USB Type-A connections and replaces traditional outlets in as little as ten minutes, providing easy-to-access charging without needing bulky adapters or sacrificing your plugs. Also features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007032222	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging
Outlet Type	Residential, Indoor, Tamper-Resistant, USB-Charging	Application Sector	Residential/Commercial
Type	Outlet		

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Is Tamper-Resistant	Yes	USB Amperage	3.1 A
---------------------	-----	--------------	-------

---

Number of USBs	2	Number of Gangs	1
----------------	---	-----------------	---

---

USB Power Output	15 W	Amperage	15 A
------------------	------	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

---

Mounting Type	Box	Voltage	125 VAC
---------------	-----	---------	---------

---