



radiant Collection  
radiant® 15A Tamper-Resistant USB Outlet, Ivory  
Part No. TM826USBICC6



Get a full battery for your phones, tablets and more with the convenience of built-in charging. This tamper-resistant USB outlet includes two USB Type-A connections and replaces traditional outlets in as little as ten minutes, providing easy-to-access charging without needing bulky adapters or sacrificing your plugs. Also features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

|   |   |
|---|---|
| Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.  | All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.   |
| Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect. | Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation. |
| More color options available to fit any style, including finishes to match current hardware and lighting trends.  | Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.            |

## Specifications

### General Info

|                   |                         |                       |   |
|-------------------|-------------------------|-----------------------|---|
| Product Line      | Pass & Seymour          | Color                 | Ivory   |
| Country Of Origin | China                   | Number of Receptacles | 2   |
| Features          | USB-A Charging          | Outlet Type           | Indoor, Residential, Tamper-Resistant, USB-Charging |
| Warranty Type     | 1-Year Limited Warranty | Type                  | Outlet  |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 1.69 in | Product Depth US | 1.35 in |
|------------------|---------|------------------|---------|

|                   |         |
|-------------------|---------|
| Product Height US | 4.18 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                     |     |              |       |
|---------------------|-----|--------------|-------|
| Is Tamper-Resistant | Yes | USB Amperage | 3.1 A |
|---------------------|-----|--------------|-------|

|                |   |                  |      |
|----------------|---|------------------|------|
| Number of USBs | 2 | USB Power Output | 15 W |
|----------------|---|------------------|------|

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

|                |        |               |     |
|----------------|--------|---------------|-----|
| Indoor/Outdoor | Indoor | Mounting Type | Box |
|----------------|--------|---------------|-----|

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|