



Pass and Seymour  
Discontinued - DEC COMBO 3W+PILOT IV CC \*\*  
Part No. TM83PLICC



## Features & Benefits

Impact-resistant face and body.

Fully rounded back body protects wires from being damaged by sharp edges.

Clear identification of circuits.

External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.

Ground screw position under the end of the strap minimizes the risk of contact.

Full wraparound metal strap with lock-in tabs.

Patented split circuit tab -- easily accessible, and can be reinstalled without a tool.

Unique "Up/Down" switches match the look and feel of standard Decorator switches.

Largest breadth of 15 amp offering.

All screws are tri-drive.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

USB Amperage	2.1 A	Amperage	15 A
--------------	-------	----------	------