



radiant Collection  
radiant® 15A Single-Pole Switch, Light Almond  
Part No. TM870LACC10



The perfect upgrade for your basic light switch, the Single-Pole Switch from the radiant® Collection provides on/off control of a light or fixture from a single location, while combining clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Replaces any standard switch with ease, in as little as 10 minutes

Uses a paddle switch for smoother control with a low-profile aesthetic

Features durable, high-impact resistant thermoplastic construction

Designed to install easily with a narrower back body and captivated mounting screws

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

## Specifications

### General Info

|                    |                         |                    |                         |
|--------------------|-------------------------|--------------------|-------------------------|
| Product Line       | Pass & Seymour          | Color              | Light Almond            |
| Finish             | Matte                   | UPC Number         | 785007858426            |
| Country Of Origin  | China                   | Switch Type        | Paddle                  |
| Number of Switches | 1                       | Application Sector | Commercial, Residential |
| Warranty Type      | 1-Year Limited Warranty | Type               | Switch                  |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.43 in | Product Depth US | 1.27 in |
| Product Height US | 4.19 in |                  |         |

---

Listing Agencies / 3rd Party Agencies

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

Technical Information

---

|                |                     |                 |             |
|----------------|---------------------|-----------------|-------------|
| Contact Rating | 15 Amp, 120/125 VAC | Number of Gangs | 1           |
| Amperage       | 15 A                | Number of Poles | Single Pole |
| Wire Size      | #14 - #10 AWG       | Mounting Type   | Box         |

---