




Pass and Seymour
Decorator Openings, Three Gang, Light Almond
Part No. TP263LA



The TradeMaster® thermoplastic 3-gang decorator wall plate provides maximum durability in plastic wall plates. Self-extinguishing nylon construction makes these wall plates virtually unbreakable. They are 3/16 of an inch higher and wider than typical plastic wall plates - not enough to be apparent to the eye, but the extra size cuts cost by reducing dry wall rework.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates; and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Wall Plate Type	Dimmer/Switch, Outlet	Application Sector	Residential/Commercial
Standard	CSA, UL514		

Dimensions

Product Width US	6.563 in	Product Depth US	0.25 in
Product Height US	4.6875 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

Technical Information

Cutout	Decorator	Thickness	0.07 in
Number of Gangs	3	Mounting Type	Exposed Screws
