



Pass and Seymour  
Power Outlet Receptacle Openings, Two Gang, Black  
Part No. TP703BK



Two Gang Power Outlet Receptacle Opening, 2.1563 inch hole for 2.125 inch diameter device - 4 mtg. holes, Light Almond Nylon.

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007261431	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL 514

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Additional Information

Product Environmental Profile Yes

### Technical Information

---

Cutout

Power Outlet

Thickness

0.07 in

---

Number of Gangs

2

Mounting Type

Exposed Screws

---