



Pass and Seymour
Power Outlet Receptacle Openings, Two Gang, Gray
Part No. TP703GRY



Two Gang Power Outlet Receptacle Opening, 2.1563' hole for 2.125''' diameter device - 4 mtg. holes, Light Almond Nylon.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

Color	Gray	UPC Number	785007275834
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	UL 514

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	143222
--------------	-----	---------------------	--------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Gangs	2	Mounting Type	Exposed Screws
Cutout	Power Outlet	Thickness	0.07 in
