



Pass and Seymour
Power Outlet Receptacle Openings, One Gang, Ivory
Part No. TP720I



OneGang Power Outlet Receptacle Opening, 1.5938" hole for 1.5625" diameter device -2 mtg. holes,White Nylon.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007275896	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL 514

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Cutout

Power Outlet

Thickness

0.07 in

Number of Gangs

1

Mounting Type

Exposed Screws
