




**Pass and Seymour**  
**Duplex Receptacle Openings, Two Gang, Ivory**  
Part No. TP82I



Trademaster Plate, double gang and duplex plate, is molded of rugged, practically indestructible self-extinguishing nylon. It is preferred for hospital, industrial, institutional, and other high-abuse applications. Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                        |                 |            |
|--------------------|------------------------|-----------------|------------|
| Product Line       | Pass & Seymour         | Color           | Ivory      |
| Country Of Origin  | United States          | Wall Plate Type | Outlet     |
| Application Sector | Residential/Commercial | Standard        | CSA, UL514 |

### Dimensions

|                   |           |                  |         |
|-------------------|-----------|------------------|---------|
| Product Width US  | 4.75 in   | Product Depth US | 0.25 in |
| Product Height US | 4.6875 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

---

|                 |            |               |                |
|-----------------|------------|---------------|----------------|
| Cutout          | Receptacle | Thickness     | 0.07 in        |
| Number of Gangs | 2          | Mounting Type | Exposed Screws |

---