



Pass and Seymour
TradeMaster® Junior Jumbo 1-Gang Nylon Wall Plate, Blank, Box Mounted, Gray
Part No. TPJ13GRY



Trademaster single gang wall plate in white, jumbo, blank box, is molded of rugged, practically indestructible self-extinguishing nylon. It is preferred for hospital, industrial, institutional, and other high-abuse applications. Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

Nominal thickness, .070 inch.

Specifications

General Info

| | | | |
|--------------------|--------------------------|-----------------|--------------|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Matte | UPC Number | 785007025309 |
| Country Of Origin | Mexico | Construction | Plastic |
| Wall Plate Size | Trademaster Junior-Jumbo | Wall Plate Type | Blank |
| Application Sector | Commercial, Residential | Standard | CSA, UL514 |
| Warranty Type | 1-Year Limited Warranty | Type | Wall Plate |

Dimensions

| | | | |
|------------------|-----------|------------------|---------|
| Product Width US | 3.3125 in | Product Depth US | 0.25 in |
|------------------|-----------|------------------|---------|

| | |
|-------------------|-----------|
| Product Height US | 5.0625 in |
|-------------------|-----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 143222 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------|---------|-----------------|---|
| Thickness | 0.07 in | Number of Gangs | 1 |
|-----------|---------|-----------------|---|

| | | | |
|----------------|--------|---------------|-------------|
| Indoor/Outdoor | Indoor | Mounting Type | Box Mounted |
|----------------|--------|---------------|-------------|

| | |
|-------------|----------|
| Orientation | Vertical |
|-------------|----------|