



Pass and Seymour
15A 125V Tamper-Resistant Receptacle with Two USB C/C Fast Charging Ports, Light Almond
Part No. TR15USBC6LA



Heavy-Duty Decorator Specification Grade USB Charging Receptacles 15A, 125V

Features & Benefits

Overall 6A charging capability with smart current-sharing technology to allow for full 3A through a singular Type-C port

With (2) USB Type-C ports to charge the latest mobile devices

Stainless steel auto-ground clips assure positive ground

Multiple color options available

Posted terminal screws and external back-wire pressure plates for more productive and reliable terminations

USB Type-C ports carry a minimum rating of 10,000 insertions

Slim design allows for installation in standard depth wall boxes

Efficient power supply meets the Department of Energy (DoE) Level VI no-load power requirement of 100mW max for external power supplies

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
--------------	----------------	-------------------	-------

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
------------------	----------	------------------	----------

Product Height US	2.677 in
-------------------	----------

Technical Information

Amperage	15 A
----------	------