



Pass and Seymour
15W Spec Grade USB Outlet, Type C, 15A, Tamper-Resistant, Light Almond
Part No. TR15USBC6LA



Heavy-Duty Decorator Specification Grade USB Charging Receptacles 15A, 125V

Features & Benefits

- Overall 6A charging capability with smart current-sharing technology to allow for full 3A through a singular Type-C port
- Posted terminal screws and external back-wire pressure plates for more productive and reliable terminations
- With (2) USB Type-C ports to charge the latest mobile devices
- USB Type-C ports carry a minimum rating of 10,000 insertions
- Stainless steel auto-ground clips assure positive ground
- Slim design allows for installation in standard depth wall boxes
- Multiple color options available
- Efficient power supply meets the Department of Energy (DoE) Level VI no-load power requirement of 100mW max for external power supplies

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007209808
Country Of Origin	China		

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
Product Height US	2.677 in		

Technical Information

Amperage	15 A
----------	------