



Pass and Seymour
20A 125V Hospital-Grade Tamper-Resistant Receptacle with USB C/C Fast Charging Ports, Ivory
Part No. TR20HUSBCC6I



20A 125A Hospital Grade Tamper-Resistant REC+2 USBC FAST CHR

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
--------------	----------------	-------------------	-------

Dimensions

Product Width US	1.693 in	Product Depth US	1.425 in
------------------	----------	------------------	----------

Product Height US	2.677 in
-------------------	----------

Technical Information

USB Amperage	6 A	Number of USBs	2
--------------	-----	----------------	---

USB Power Output	15 W	Amperage	20 A
------------------	------	----------	------