



Tamper-Resistant Commercial Grade Receptacle, 20A, 125V, BrownFor detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

Auto-ground clip assures positive ground.

Backed-out tri-drive steel terminal screws. Side wire only.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

High Impact resistant nylon face.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Ivory	UPC Number	785007241624
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	125 V
-----------------	-------------	---------	-------

Connection	Wire Ground	Wire Size	4 AWG
Number of Wires	3		
