



Pass and Seymour
15A 125V Spec-Grade Tamper-Resistant Decorator Duplex Receptacle, Side Wire, Black
Part No. TR26242BK



Tamper-Resistant Decorator Spec Grade Receptacle, Side Wire Only, 15amp 125volt, Black

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

AC receptacles available in 15 and 20A, 125V.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive steel terminal screws. Side wire only.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|--------------------------------------|-----------------------|--------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Commercial, Indoor, Tamper-Resistant | Type | Outlet |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.37 in | Product Depth US | 0.93 in |
| Product Height US | 3.28 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|-----|----------|------|
| Is Tamper-Resistant | Yes | Amperage | 15 A |
|---------------------|-----|----------|------|

| | | | |
|-----------------|-------------|----------------|--------|
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
|-----------------|-------------|----------------|--------|

| | |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|
