



Tamper-Resistant Heavy-Duty Decorator Spec Grade Single Receptacle, Back and Side-Wire, 15A, 125A

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007004946
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
---------------------	--------------------------	------------	--------------------

Number of Wires	3	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
Number of Poles	Double Pole	Wire Size	#14 - #10
Voltage	125 V	Environmental Conditions	Flammability: UL94 V2