



Tamper-Resistant Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 15amp 125volt BrownFor detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Internal screw-pressure-plate back and side wire capability.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Auto-ground clip assures positive ground.

Backed-out tri-drive brass terminal screws for faster installation.

Two back wire holes for additional wiring flexibility.

.032 inch thick brass triple-wipe power contacts.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |            |              |                |
|--------------------|------------|--------------|----------------|
| Color              | Gray       | UPC Number   | 785007277319   |
| Country Of Origin  | Mexico     | Product Line | Pass & Seymour |
| Application Sector | Commercial | Standard     | UL 498         |

### Listing Agencies / 3rd Party Agencies

|              |     |                     |        |
|--------------|-----|---------------------|--------|
| cULus Listed | Yes | cULus ListingNumber | 140596 |
|--------------|-----|---------------------|--------|

### Technical Information

---

|                 |             |           |          |
|-----------------|-------------|-----------|----------|
| Number of Poles | Double Pole | Voltage   | 125 V    |
| Phase           | 3           | Wire Size | 10-14Awg |
| Number of Wires | 3           |           |          |

---