



Features & Benefits

- 2.1 A USB type A receptacle charges faster than other USB receptacles eliminates the need for bulky AC adapters. **Compact Design Tamper-Resistant receptacle and two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.**
- Back and side wire terminals accommodates #14 AWG - #10 AWG stranded and solid wire. **Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code: Tamper-Resistant requirements.**
- Stainless steel auto-ground clip assures positive ground. **Zink-plated ground terminal screw**
- For covering patents, see www.legrand.us/patents. **Wire Size: #14 - #10 AWG Copper Conductor Only**

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	TR5362USBLA
Color	Light Almond	Country Of Origin	China
Application Sector	Commercial	Standard	CSA Listed, ETL Lsted, FSUL, UL Listed, RoHS

Additional Information

Product Environmental Profile Yes

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Phase	Single	Connection	Side & Back Wired

Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	125.0 V
Environmental Conditions	UL94 V2		
