



Pass and Seymour
3.1A Spec Grade USB Outlet, Type A, 20A, Tamper-Resistant, Black
Part No. TR5362USBBK



Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

| | |
|--|---|
| Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices. | One-piece heat-treated triple-wipe brass power contacts. |
| AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects. | Multiple color options available. |
| Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire. | Stainless steel auto-ground clips assure positive ground. |
| Wire Size: #14 - #10 AWG Copper Conductor Only | |

Specifications

General Info

| | | | |
|--------------------|-------------------------|-----------------------|---|
| Product Line | Pass & Seymour | Color | Black |
| Finish | Matte | UPC Number | 785007031706 |
| Country Of Origin | Vietnam | Number of Receptacles | 2 |
| Features | USB-A Charging | Outlet Type | Tamper-Resistant, USB-Charging |
| Application Sector | Commercial | Standard | CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC |
| Warranty Type | 1-Year Limited Warranty | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.693 in | Product Depth US | 1.392 in |
| Product Height US | 2.677 in | | |

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|---------------------|--------------------------|---------------------|--------------|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
| USB Amperage | 3.1 A | Number of USBs | 2 |
| USB Power Output | 15 W | Temperature Rating | -40° - 60° C |
| Amperage | 20 A | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |